

[See all 8 Products in Family](#)

M30.5 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock #12-482 **20+ In Stock**

C\$47⁹⁵

ADD TO CART

Volume Pricing	
Qty 1-9	C\$47.95 each
Qty 10-25	C\$43.26 each
Need More?	Request Quote

Product Downloads

Filter Adapter	Type:
M42 x 0.75 (T-Mount)	Inner Thread:
M30.5 x 0.5	Outer Thread:
48.0	Outer Diameter (mm):
T-Mount to M30.5 x 0.5	Thread Type:

27.5 **Clear Aperture CA (mm):**

5.5 **Mount Thickness (mm):**

8.0 **Total Thickness with Thread (mm):**

Thread Adapter **Function:**

Filter Sold Separately **Note:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Product Details

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.