

M30.5 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-482** 20+ In Stock

-

1

+

C\$47⁹⁵

ADD TO CART

Volume Pricing	
Qty 1-9	C\$47.95 each
Qty 10-25	C\$43.26 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Filter Sold Separately

Note:

Filter Adapter

Type:

Thread Adapter

Function:

Physical & Mechanical Properties	
27.5	Clear Aperture CA (mm):
48.0	Outer Diameter (mm):
8.0	Total Thickness with Thread (mm):
Threading & Mounting	
T-Mount to M30.5 x0.5	Thread Type:
M42 x0.75 (T-Mount)	Inner Thread:
5.5	Mount Thickness (mm):
M30.5 x0.5	Outer Thread:
Regulatory Compliance	
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.