

M35.5 x 0.50 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-579 [CONTACT US](#)

- 1 + **C\$100.80**

ADD TO CART

Qty 1-9
C\$100.80
Qty 10+
C\$96.46
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
30.50

Coating:
Hardcoated

Diameter (mm):
37.50

Extinction Ratio:
up to 3000:1 @ ~600nm (nominal)

Filter Thread: M35.5 x0.50
Surface Quality: 40-20
Type: Mounted Imaging Filter
Construction: Black Anodized Aluminum
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 9.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

