

M39.0 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-486** 20+ In Stock

-

1

+

C\$47⁹⁵

ADD TO CART

Volume Pricing	
Qty 1-9	C\$47.95 each
Qty 10-25	C\$43.26 each
Need More?	Request Quote

Product Downloads

General	
Filter Sold Separately	Note:
Filter Adapter	Type:

Thread Adapter	Function:
----------------	-----------

Physical & Mechanical Properties	
Clear Aperture CA (mm):	

36.0	
	Outer Diameter (mm):
48.0	
	Total Thickness with Thread (mm):
8.0	
Threading & Mounting	
	Thread Type:
T-Mount to M39.0 x 0.5	
	Inner Thread:
M42 x 0.75 (T-Mount)	
	Mount Thickness (mm):
5.5	
	Outer Thread:
M39.0 x 0.5	
Regulatory Compliance	
	Certificate of Conformance:
View	
	Reach 240:
Compliant	

Product Details

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.