

M46 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock **#21-647** ☐ In Stock

1 **C\$107.10**

ADD TO CART

Qty 1-9
C\$107.10
Qty 10+
C\$102.62
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
41.00

Coating:
Hardcoated

Diameter (mm):
48.00

Extinction Ratio:
up to 3000:1 @ ~600nm (nominal)

Filter Thread: M46 x0.75
Surface Quality: 40-20
Type: Mounted Imaging Filter
Construction: Black Anodized Aluminum
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 9.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

