

M6 x 1.0 Bumper (Package of 4), Sorbothane Bumpers

Stock #56-923 **11 In Stock**



1

C\$67^{.55}

ADD TO CART



Volume Pricing	
Qty 1-2	C\$67.55 each
Qty 3+	C\$59.92 each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	eDrawing:eprt
EO Spec Sheet	Download All

General

Type: Metric

Note: Thread Type: M6

Physical & Mechanical Properties

Thickness (mm): 25.40

Construction: Sorbothane

Diameter (mm): 38.10

Load Capacity (lbs): 30-65 / bumper

Threading & Mounting

Thread Length (mm): 12.7

Regulatory Compliance

RoHS 2015: [Compliant](#)

Reach 211: [Compliant](#)

Certificate of Conformance: [View](#)

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (¼-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. ¼-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
--	-------	---------	--------------	-------	-----

MORE+

English Leveling Feet, 32-500lb Support
(Package of 4)

#62-682

C\$39.55
Request Quote

4 In Stock

1



Related Products



English and Metric Breadboards



Self-Adjusting Leveling Feet



#39-346 - Large Workstation Platform
C\$471.80

Qty



#53-009 - Small Platform Base
C\$471.80

Qty



Frequently Purchased Together



#03-655 - Sliding 2" x 3" Base Plate
C\$35.35

Qty



#03-665 - V-Block Base with Clamps
C\$427.00

Qty



#03-668 - 2.0 - 35.0mm Optic Dia., Three-Screw Adjustable Ring Mount
C\$88.20

Qty



#03-640 - 24" x 12", Breadboard
C\$541.80

Qty



Resources

Media Type

- FAQ
- Glossary
- Application Note
- Trending in Optics
- Video

? FAQ

Do you have any components that would...

? FAQ

Do your iris diaphragms have mounts for...

GLOSSARY

Axial Runout

GLOSSARY

Concentricity

GLOSSARY

Inverted Load Capacity

GLOSSARY

Tangent Arm Drive



[View More](#)

;