

M86 x 1.00 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-902** ☒ In Stock

-

1

+

C\$203.00

ADD TO CART

Qty 1-9
C\$203.00
Qty 10+
C\$187.32
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 80.00
Coating: Uncoated
Diameter (mm): 90.00 +0/-0.2
Extinction Ratio:

Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Filter Thread:
M86 x 1.00

Substrate: ☐
Float Glass

Operating Temperature (°C):
-15 to +70

Polarization:
95% Efficiency

Transmission (%):
Single: 30
Crossed: 0.15

Type:
Mounted Imaging Filter

Construction:
Dichroic

Mount Thickness (mm):
9 ±0.1

Wavelength Range (nm):
400 - 700

Mount Thickness Including Threads (mm):
11

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)