

TECHSPEC[®] C-Mount, 25mm Cube Mount



Stock **#56-263** [CONTACT US](#)

-

1

+

C\$408^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$408.80 each
Qty 5-9	C\$360.78 each
Qty 10-25	C\$332.08 each
Need More?	Request Quote

Product Downloads

General

Function:

Optic Munt (Fixed)

Type of Optics:

Cube

Note:

Includes one C-Mount Aperture Cap [\(#55-245\)](#)

Dimensions of Compatible Optics (mm):

25.0 Sq.

Physical & Mechanical Properties	
38.0 x 38.0 x 50.0	Dimensions (mm):
38.0	Extension Length (mm):
25.0	Min. Thickness of Compatible Optics (mm):
25.0	Max. Thickness of Compatible Optics (mm):
Threading & Mounting	
C-Mount	Thread Type:
1/4-20	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

