

TECHSPEC® C-Mount, 35mm Sq. x 3mm Thick Plate Mount



Mount Only (no optics included) for any 35mm sq x 3mm Thick Plate, #56-265

Stock **#56-265** **4 In Stock**

- 1 + C\$408⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | C\$408.80 each |
| Qty 5-9 | C\$360.78 each |
| Qty 10-25 | C\$332.08 each |
| Need More? | Request Quote |

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Square

Note:
Includes one C-Mount Aperture Cap ([#55-245](#))

Dimensions of Compatible Optics (mm):
35.0 Sq.

Physical & Mechanical Properties

Dimensions (mm):
38.0 x 38.8 x 50.0

Extension Length (mm):
38.0

Min. Thickness of Compatible Optics (mm):
3.00

Max. Thickness of Compatible Optics (mm):
6.00

Threading & Mounting

Thread Type:
C-Mount

Compatible Post:
1/4-20

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

