

Mounted M22.5 x 0.5 Threaded - Green Filter



Stock **#46-540** ☐ In Stock

-

1

+

C\$66.50

ADD TO CART

Qty 1-9
C\$66.50
Qty 10+
C\$61.74
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 18.5
Filter Thread: M22.5 x 0.50
Color: Green
Cut-Off Wavelength (nm): 550.00

Cut-On Wavelength (nm): 520.00
Glass/Filter Number: G-533
Index of Refraction n_d: 1.54
Note: AR Coating: MgF ₂
Outer Diameter (mm): 24.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya G-533 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View