

Mounted M30.5 x 0.5 Threaded - Red Filter



Stock **#46-545** ☐ In Stock

-

1

+

C\$74.90

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$74.90                      |
| Qty 10+                       |
| C\$69.16                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Clear Aperture CA (mm):  
27.0

Filter Thread:  
M30.5 x 0.50

Color:  
Red

Cut-On Wavelength (nm):  
600.00

|                                                             |
|-------------------------------------------------------------|
| <b>Glass/Filter Number:</b><br>R-60                         |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.53        |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                |
| <b>Outer Diameter (mm):</b><br>32.0                         |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Substrate Thickness (mm):</b><br>2.0                     |
| <b>Surface Quality:</b><br>80-50                            |
| <b>Thickness of Compatible Optics (mm):</b><br>2.0          |
| <b>Thickness with Mount (mm):</b><br>5.00                   |
| <b>Type:</b><br>Mounted Imaging Filter                      |
| <b>Type of Filter:</b><br>Hoya R-60 or equivalent           |
| <b>Wavelength Range (nm):</b><br>400 - 700                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |