

[See all 17 Products in Family](#)

Mounted M40.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock **#54-725** CLEARANCE **20+ In Stock**

-

1

+

C\$65¹⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$65.10 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter

Type:

Physical & Mechanical Properties

37.0

Clear Aperture CA (mm):

42.0

Outer Diameter (mm):

5.00

Thickness with Mount (mm):

2.00 ±0.2	Thickness (mm):
Optical Properties	
390.00	Cut-On Wavelength (nm):
L-39	Glass/Filter Number:
Hoya L-39	Substrate: ☐
AR Coated	Coating:
Clear	Color:
80-50	Surface Quality:
R _{avg} >2% @ 400 - 700nm	Coating Specification:
350 - 2200	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Threading & Mounting	
M40.5 x0.50	Filter Thread:
Environmental & Durability Factors	
-15 to +70	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information

