

## Mounted M46 x 0.75 Threaded - Green Filter



Stock #54-768 ☐ In Stock

1

C\$79.10

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$79.10                      |
| Qty 10+                       |
| C\$73.50                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

|                                    |
|------------------------------------|
| Clear Aperture CA (mm):<br>41.5    |
| Filter Thread:<br>M46 x0.75        |
| Color:<br>Green                    |
| Cut-Off Wavelength (nm):<br>550.00 |

|                                                                                                                      |
|----------------------------------------------------------------------------------------------------------------------|
| <b>Cut-On Wavelength (nm):</b><br>520.00                                                                             |
| <b>Glass/Filter Number:</b><br>G-533                                                                                 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.54                                                                 |
| <b>Mount Thickness (mm):</b><br>4.4 ±0.1                                                                             |
| <b>Mount Thickness Including Threads (mm):</b><br>6.4                                                                |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                                                                         |
| <b>Outer Diameter (mm):</b><br>48.0                                                                                  |
| <b>Substrate:</b> <br>Colored Glass |
| <b>Substrate Thickness (mm):</b><br>2.5                                                                              |
| <b>Surface Quality:</b><br>80-50                                                                                     |
| <b>Thickness of Compatible Optics (mm):</b><br>2.5                                                                   |
| <b>Thickness with Mount (mm):</b><br>5.00                                                                            |
| <b>Type:</b><br>Mounted Imaging Filter                                                                               |
| <b>Type of Filter:</b><br>Hoya G-533 or equivalent                                                                   |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |