

Mounted M52 x 0.75 Threaded - Blue Filter



Stock #54-776 CLEARANCE ☐ In Stock

- 1 +

C\$34.93

ADD TO CART

Qty 1+
C\$34.93

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 48.0
Filter Thread: M52 x0.75
Color: Blue
Cut-Off Wavelength (nm): 480.00
Cut-On Wavelength (nm): 395.00

Glass/Filter Number: B-440
Index of Refraction n_d: 1.55
Note: AR Coating: MgF ₂
Outer Diameter (mm): 54.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya B-440 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View