

Mounted M58 x 0.75 Threaded - Green Filter



Stock #54-771 ☐ In Stock

1

C\$79.10

ADD TO CART

Qty 1-9
C\$79.10
Qty 10+
C\$73.50
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
54.0

Filter Thread:
M58 x 0.75

Color:
Green

Cut-Off Wavelength (nm):
550.00

Cut-On Wavelength (nm): 520.00
Glass/Filter Number: G-533
Index of Refraction n_d: 1.54
Mount Thickness (mm): 4.6 ±0.1
Mount Thickness Including Threads (mm): 6.8
Note: AR Coating: MgF ₂
Outer Diameter (mm): 60.0
Substrate:  Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya G-533 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View