

## Mounted M62 x 0.75 Threaded - Green Filter



Stock **#46-533** ☒ In Stock

1

C\$85.40

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$85.40                      |
| Qty 10+                       |
| C\$79.38                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Clear Aperture CA (mm):  
58.7

Filter Thread:  
M62 x0.75

Color:  
Green

Cut-Off Wavelength (nm):  
550.00

|                                                                                                                      |
|----------------------------------------------------------------------------------------------------------------------|
| <b>Cut-On Wavelength (nm):</b><br>520.00                                                                             |
| <b>Glass/Filter Number:</b><br>G-533                                                                                 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.54                                                                 |
| <b>Mount Thickness (mm):</b><br>4.9 ±0.1                                                                             |
| <b>Mount Thickness Including Threads (mm):</b><br>7.4                                                                |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                                                                         |
| <b>Outer Diameter (mm):</b><br>65.0                                                                                  |
| <b>Substrate:</b> <br>Colored Glass |
| <b>Substrate Thickness (mm):</b><br>2.5                                                                              |
| <b>Surface Quality:</b><br>80-50                                                                                     |
| <b>Thickness of Compatible Optics (mm):</b><br>2.5                                                                   |
| <b>Thickness with Mount (mm):</b><br>5.00                                                                            |
| <b>Type:</b><br>Mounted Imaging Filter                                                                               |
| <b>Type of Filter:</b><br>Hoya G-533 or equivalent                                                                   |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |