

SCHOTT N-WG-305, 50mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#66-073** ☐ In Stock



1



C\$123.20

ADD TO CART

Qty 1-10

C\$123.20

Qty 11+

C\$109.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
309±6

Cut-On Wavelength (nm):

309.00
Density (g/cm³): 2.51
Glass/Filter Number: SCHOTT N-WG305
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 420.00
Spectral Transmittance t_p (%): 99.00
Stopband Limit λ_s (nm): 260.00
Surface Quality: 80-50
Transformation Temperature (°C): 562.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View