

[See all 2 Products in Family](#)

Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 6cc

See More by [Norland](#)



Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 6cc

Stock **#17-407** **13 In Stock**

-

1

+

C\$42^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$42.00 each
Qty 5-11	C\$37.80 each
Need More?	Request Quote

Product Downloads

General	
0.20	Size (oz):
IML 150	Norland Number:
8 months	Shelf Life:
Barrel	Type:

Optical Properties	
1.52	Index of Refraction (n _d):
Material Properties	
100	Viscosity (cps):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 251:

Product Details

- 1.52 Index of Refraction at 589nm
 - Ideal for Temporary Fiber Slicing
 - 6g or 30g Preloaded Syringes
- Norland Index Matching Liquid (IML) 150 is a low viscosity liquid monomer used as an index matching media for temporary fiber slicing. Unlike silicone index matching liquids which are difficult to completely remove from a fiber end after use, IML 150 is easily removed using acetone. This index matching liquid can also be used between two optical elements to eliminate reflection losses caused by glass-air interfaces. Norland Index Matching Liquid (IML) 150 is available in preloaded syringes with either 6g or 30g of liquid. IML 150 does not cure and will always remain a liquid.