

NUV M35.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-570** ☐ In Stock

-

1

+

C\$203.00

ADD TO CART

Qty 1-9
C\$203.00
Qty 10+
C\$193.62
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-250, 400-660

Clear Aperture CA (mm):
30.50

Coating:
Hard Coated

Filter Thread:

M35.5 x 0.50
Color: NUV
Center Wavelength CWL (nm): 324.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 105.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 37.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View