

Olympus LMPLFLN-BD 100X Objective

See More by [Olympus](#)



Stock **#86-831** [CONTACT US](#)

- 1 + **C\$11,312.00**

ADD TO CART

Qty 1+
C\$11,312.00

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm): N/A
Diameter (mm): 32.00
Field of View (mm): 0.26
Focal Length FL (mm): 1.80
Model Number: 1-U2N354

Length excluding Threads (mm): 41.70
Magnification: 100X
Maximum Diameter (mm): 32
Numerical Aperture NA: 0.80
Mounting Threads: M26 x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.42
Depth of Field (µm): 0.43
Working Distance (mm): 3.3
Weight (g): 102
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--