

[See all 14 Products in Family](#)

Olympus PLN 10X Objective

See More by [Olympus](#)



#86-813

Stock **#86-813** 2 In Stock

-

1

+

C\$579^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	C\$579.60 each
Need More?	Request Quote

Product Downloads

General	
1-U2B223	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm	
Microscope Objective	Type:
Infinity Corrected	Style:
	Manufacturer:

Physical & Mechanical Properties

2.2	Field of View (mm):
34.30	Length excluding Threads (mm):
24	Maximum Diameter (mm):
80.1	Weight (g):

Optical Properties

N/A	Compatible Cover Glass Thickness (mm):
18.00	Focal Length FL (mm):
10X	Magnification:
0.25	Numerical Aperture NA:
1.34	Resolving Power (µm):
4.40	Depth of Field (µm):
10.6	Working Distance (mm):
22	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
440	Depth of Focus (µm):

Threading & Mounting

RMS / 20.32mm x 36 TPI	Mounting Threads:
------------------------	-------------------


Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------


Product Details

- Ideal for Brightfield, Darkfield, or Fluorescence Microscopy
 - Excellent Price-to-Performance Ratio
 - Suitable for Introductory and Advanced Optical Microscopy Applications
 - Additional [Olympus Infinity Corrected Objectives](#) Available
- Olympus Plan Achromatic Objectives are designed for clinical laboratory or examination applications. When using brightfield observation in a transmitted illumination system, Olympus Plan Achromatic Objectives provide excellent field flatness of up to F.N.22.

Technical Information



Using Olympus Objectives
with C-Mount Cameras



	Stock #	A	B	C	D	E	F	G
PLN 2X	16-879	39.1	3.4	0.0	16.8	16.8	24.0	4.5
PLN 4X	86-812	26.4	4.4	0.0	15.8	15.8	24.0	4.5
PLN 10X	86-813	34.3	4.1	1.6	10.5	16.0	24.0	4.5
PLN 20X	86-814	43.7	4.2	2.4	6.1	15.6	24.0	4.8
PLN 40X	86-815	44.3	4.2	3.0	7.5	15.6	24.0	4.5
PLN 100X	86-816	44.7	4.2	2.5	6.6	15.6	24.0	4.5

