

Olympus UPLXAPO 100X Oil Immersion Objective

See More by [Olympus](#)



Olympus X-Line Extended Apochromat Objectives



Stock **#14-910** ☐ In Stock

- 1 + **C\$10,831.80**

ADD TO CART

Qty 1+
C\$10,831.80

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
0.265

Focal Length FL (mm):
1.80

Model Number:

UPLXAPO100XO
Length excluding Threads (mm): 44.92
Magnification: 100X
Maximum Diameter (mm): 30.5
Numerical Aperture NA: 1.45
Mounting Threads: RMS / 20.32mm x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (μm): 0.23
Depth of Field (μm): 0.20
Working Distance (mm): 0.135
Weight (g): 161
Note: Spring-loaded. Recommended Immersion Oil #86-834
Wavelength Range (nm): 300 - 1000
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: Oil

Regulatory Compliance

Certificate of Conformance: View
--