

Preloaded Norland Optical Adhesive NOA 86TH Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-391** [CONTACT US](#)

- 1 + **C\$37.10**

ADD TO CART

Qty 1-4
C\$37.10
Qty 5+
C\$35.56
Volume Pricing
Request Quote

Get Product Downloads

Size (oz): 0.1
Glass Bonding: Excellent
Metal Bonding: Good

Plastic Bonding: Excellent/Good
Viscosity (cps): 20000 - 25000
Durability: Hard
Index of Refraction n_d: 1.54
Norland Number: 86TH
Shelf Life: 4 months
Type: Barrel
Typical Applications: Applications requiring adheisve meeting Bellcore specification of 85C/85RH for bonding glass for 2000 hours
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 315 - 420
Bonding Type: Glass to Glass/Plastic
Energy for Full Cure (J/cm²): 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant