

# Hoya R72 (720nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#66-057** ☐ In Stock

-

1

+

C\$61.60

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| C\$61.60                      |
| Qty 11+                       |
| C\$54.60                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.40

Cut-Off Position  $\lambda_c$  (nm):  
720±9

Cut-On Wavelength (nm):  
720.00 ±9

|                                                      |
|------------------------------------------------------|
| Density (g/cm³):<br>2.86                             |
| Glass/Filter Number:<br><a href="#">Hoya R72</a>     |
| Substrate: <input type="checkbox"/><br>Colored Glass |
| Coating:<br>Uncoated                                 |
| Color:<br>Black                                      |
| Surface Quality:<br>80-50                            |
| Transformation Temperature (°C):<br>525              |
| Thickness (mm):<br>2.50                              |
| Thickness Tolerance (mm):<br>±0.2                    |
| Type:<br>Longpass Filter                             |
| Wavelength:<br>IR                                    |
| Dimensional Tolerance (mm):<br>±0.38                 |
| Reflection Factor P <sub>d</sub> :<br>0.92           |
| Bevel:<br>Protective as needed                       |
| Δλ (nm):<br><45                                      |
| TH (%):<br>>85                                       |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Exempt</a>                |
| Reach 224:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |