

Red Laser Pointer



Stock **#53-546** 12 In Stock

-

1

+

C\$44^{.80}

ADD TO CART

Volume Pricing	
Qty 1+	C\$44.80 each
Need More?	Request Quote

Product Downloads



General

Type of Laser:	
Diode	
Laser Class - CDRH:	
3R	
Operating Lifetime (hours):	
3.00	

Physical & Mechanical Properties

Length (mm):	
133.35	

Optical Properties	
650.00	Wavelength (nm):
±10	Wavelength Tolerance (nm):
3.175	Beam Diameter (mm):
Red	Color:
Electrical	
5	Output Power (mW):
Hardware & Interface Connectivity	
2 AAA(not included)	Power Requirement:
Free Space	Output Type:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

Point out desired targets as far away as 500 yards (1500 ft.). Designed with the push button at the front to allow for better stability during your presentations. Operates on 2 AAA batteries (not included). Aluminum construction with smooth, matte black finish. Pen-sized, it fits comfortably in your hand or pocket. The spot size is 1" Dia. at 75 ft. and 2" Dia. at 165 ft. Includes a 2-year manufacturer's limited warranty.

This compact red laser pointer is ideal for alignment, presentation, and basic positioning applications. Emitting a high-visibility red laser beam at 650nm, it's well-suited for use in classrooms, labs, and light industrial settings. The sleek, pen-style housing allows for comfortable handheld operation, while the integrated momentary power button provides intuitive on-demand control. Designed for convenience, this red laser pointer fits easily in a pocket or toolkit. Whether you're highlighting key points in a presentation or aligning optical components, this red laser offers reliable performance in a user-friendly design.

- 650nm Wavelength
- Handheld
- Battery Powered

Handheld laser pointers project visible targets up to 500 yards (1,500 ft.). A front-positioned push button ensures steady control during presentations, while the pen-sized design fits comfortably in your hand or pocket. Each pointer operates on two AAA batteries, built with sleek metal construction and a smooth finish. Please check product details for battery inclusion.