


SCHOTT RG9, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-903** ☐ In Stock

-

1

+

C\$38.50

ADD TO CART

Qty 1-10
C\$38.50
Qty 11+
C\$37.45
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 25.40
Cut-On Wavelength (nm): 726.00
Density (g/cm³):

2.58
Full Width-Half Max FWHM (nm): 315.00
Glass/Filter Number: SCHOTT RG9
Coating: Uncoated
Color: Black
Index of Refraction n_d : 1.52
Surface Quality: 80-50
Transformation Temperature (°C): 519
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.38

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View