

# Rodagon 135mm FL - Video Lens



Lens + Modular Focus Tube + Basler Line Scan Camera

Stock **#14-704** [CONTACT US](#)

- 1 +

**C\$1,295.00**

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| C\$1,295.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):  
95.4

Iris Option:  
Variable

Length (mm):  
45.50

Horizontal Field of View, 1/2" Sensor:  
2.6°

|                                                                                                                                                                                                                                                                                                       |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Filter Thread:</b><br>M40.5 x 0.50                                                                                                                                                                                                                                                                 |
| <b>Maximum Diameter (mm):</b><br>50.0                                                                                                                                                                                                                                                                 |
| <b>Maximum Image Circle (mm):</b><br>174.00                                                                                                                                                                                                                                                           |
| <b>Note:</b><br>Requires Leica Lens Adapter M39 x 1/26" for 135mm Lens <a href="#">#54-126</a> , Modular Focus Tube <a href="#">#14-707</a> , and a lens mount adapter ( <a href="#">C-Mount</a> , <a href="#">F-Mount</a> , <a href="#">T-Mount</a> , <a href="#">SLR</a> , or <a href="#">M72</a> ) |
| <b>Type:</b><br>Fixed Focal Length Lens                                                                                                                                                                                                                                                               |
| <b>Focal Length FL (mm):</b><br>135.00                                                                                                                                                                                                                                                                |
| <b>Primary Magnification PMAG:</b><br>0.07X                                                                                                                                                                                                                                                           |
| <b>Maximum Sensor Format:</b><br>174mm (Image Circle)                                                                                                                                                                                                                                                 |
| <b>Working Distance (mm):</b><br>2,128 - ∞                                                                                                                                                                                                                                                            |
| <b>Mount:</b><br>Adapter Required                                                                                                                                                                                                                                                                     |
| <b>Aperture (f/#):</b><br>f/5.6 - f/32                                                                                                                                                                                                                                                                |
| <b>Lens Wavelength Range:</b><br>VS                                                                                                                                                                                                                                                                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |