

**TECHSPEC® 25mm ID Rotary Mount, 1/4-20**



Rotary Mount, 1/4-20, #87-529

Stock **#87-529** **1 In Stock**

⊖ 1 ⊕ C\$186.20

**ADD TO CART**

Volume Pricing

Qty 1+	C\$186.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Rotary **Function:**

Circular/Cylindrical Tube **Type of Optics:**

**Physical & Mechanical Properties**

25.0 **Plate Inner Diameter (mm):**

38.0 **Bolt Circle Diameter for 6mm Dia. Thru (mm):**

Black Anodized Aluminum **Construction:**

50 Dia. **Dimensions (mm):**

21.00 **Thickness (mm):**

38.0 **Bolt Circle Diameter for M3 Tapped (mm):**

## Threading & Mounting

1/4-20 **Compatible Post:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

## Product Details

- Specialized Plates Designed to Hold and Position Optics
- Anodized Aluminum Construction with Stainless Steel Screws
- X-Y Micro Positioning Plate with RMS Mounting Thread

TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or 1/4-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.