

TECHSPEC[®] 25mm ID Rotary Mount, M6



Rotary Mount, M6, #85-658

Stock **#85-658** 5 In Stock

-

1

+

C\$182²⁸

ADD TO CART

Volume Pricing	
Qty 1+	C\$182.28 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Rotary	Function:
Circular/Cylindrical Tube	Type of Optics:

Physical & Mechanical Properties

25.0	Plate Inner Diameter (mm):
38.0	Bolt Circle Diameter for 6mm Dia. Thru (mm):
Black Anodized Aluminum	Construction:
50 Dia.	Dimensions (mm):
21.00	Thickness (mm):
38.0	Bolt Circle Diameter for M3 Tapped (mm):
Threading & Mounting	
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Specialized Plates Designed to Hold and Position Optics
 - Anodized Aluminum Construction with Stainless Steel Screws
 - X-Y Micro Positioning Plate with RMS Mounting Thread
- TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or ¼-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.