

Rotary Mount with 4" Post



Rotary Mount with 4" Post and Mounted Polarizer, #52-574



Stock **#52-573** 1 In Stock

-

1

+

C\$249⁻²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$249.20 each
Qty 5+	C\$224.28 each
Need More?	Request Quote

Product Downloads

General

Type:

Adjustable - Rotary

Contents of Kit:

Rotary Mount ([#52-572](#))
4" Long 1/4-20 Steel Post ([#59-000](#))

Physical & Mechanical Properties

90°-0-90° with 1° increments	
Scale Divisions:	
Black Anodized Aluminum with Steel Post	
Construction:	
360	
Travel (°):	
Threading & Mounting	
M42 x 0.75 (T-Mount)	
Thread Type:	
1/4-20	
Compatible Post:	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 223:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- Manual 360° Rotation
- Locking Thumb Screw for Secure Positioning and Alignment
- Compatible with [T-Mount Optic Mounts](#)

The Rotary Optic Mount allows smooth manual 360° rotation of optics for easy relative angular positioning. An ideal alternative for expensive rotary translation stages, this rotary optic mount can be used for aligning prisms, beamsplitters, polarizers and other optical components using a 180° (90°-0-90°) scale with 1° increments. The mount is compatible with [T-Mount Optic Mounts](#). The Rotary Optic Mount is constructed of black anodized aluminum with a stainless-steel lever. [#52-573](#) includes a 4" long stainless steel mounting post [#59-000](#).

Technical Information

