

Rotary Mount



#52-572

Stock **#52-572** **7 In Stock**

⊖ 1 ⊕ C\$249⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	C\$249.20 each
Qty 5+	C\$224.28 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Rotary **Type:**

Physical & Mechanical Properties

90°-0-90° with 1° increments **Scale Divisions:**

Black Anodized Aluminum **Construction:**

Travel (°):

Threading & Mounting

M42 x 0.75 (T-Mount)	Thread Type:
1/4-20	Compatible Post:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Manual 360° Rotation
- Locking Thumb Screw for Secure Positioning and Alignment
- Compatible with [T-Mount Optic Mounts](#)

The Rotary Optic Mount allows smooth manual 360° rotation of optics for easy relative angular positioning. An ideal alternative for expensive rotary translation stages, this rotary optic mount can be used for aligning prisms, beamsplitters, polarizers and other optical components using a 180° (90°-0-90°) scale with 1° increments. The mount is compatible with [T-Mount Optic Mounts](#). The Rotary Optic Mount is constructed of black anodized aluminum with a stainless-steel lever. [#52-573](#) includes a 4" long stainless steel mounting post [#59-000](#).

Technical Information

