



Hoya RT830 (IR) 50.8mm Square, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#46-444** ☐ In Stock

1 **C\$151.20**

ADD TO CART

Qty 1-10
C\$151.20
Qty 11+
C\$134.40
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Center Wavelength CWL (nm):
830.00

Density (g/cm³): 2.75
Full Width-Half Max FWHM (nm): 260.00
Glass/Filter Number: Hoya RT830
Substrate: ☐ Colored Glass
Length (mm): 50.80
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: IR
Width (mm): 50.80
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View
