

TECHSPEC® S-Mount Extension Tube Kit



#68-226: S-Mount Extension Tube Kit

Stock **#68-226 2 In Stock**

⊖ 1 ⊕ C\$291⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$291.20 each
Qty 5-9	C\$257.88 each
Qty 10-25	C\$237.72 each
Need More?	Request Quote

Product Downloads

General

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

Contents of Kit:
3 Each of [#63-955](#), [#63-956](#), [#63-957](#), [#63-958](#)

Physical & Mechanical Properties

10.0 Clear Aperture CA (mm):

16.0 Outer Diameter (mm):

Threading & Mounting

S-Mount Thread Type:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

;