

Schneider 60mm F-Mount Lens



Stock **#34-234** ☐ In Stock

1 **C\$2,842.00**

ADD TO CART

Qty 1+
C\$2,842.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
117 (35mm Sensor)

Iris Option:
Variable

Length (mm):
32.60

Filter Thread:
M43.0 x0.75

Maximum Diameter (mm):
49.0

Weight (g): 280.00
Maximum Rear Protrusion (mm): 8.9
Maximum Image Circle (mm): 60.00
Horizontal Field of View, 35mm Sensor: 39.5°
Note: Optimized Working Distance: 276mm - ∞
Type: Fixed Focal Length Lens
Focal Length FL (mm): 60.00
Maximum Sensor Format: 60mm (Image Circle)
Working Distance (mm): 200 - ∞
Mount: F-Mount
Aperture (f/#): f/4.0 - 4/16
Distortion (%): <0.6
Coating: 400 - 1000 BBAR
Lens Wavelength Range: VIS-NIR Color Corrected

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant