



SCHOTT BG25, 50mm Sq., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-413** ☐ In Stock

-

1

+

C\$123.20

ADD TO CART

Qty 1-10
C\$123.20
Qty 11+
C\$109.20
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 400.00
Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT BG25
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Violet
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 487
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-Vis
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View