



SCHOTT BG36, 12.5mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-370** [CONTACT US](#)



1



C\$100.80

ADD TO CART

Qty 1-10

C\$100.80

Qty 11+

C\$88.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Density (g/cm³):
3.59

Glass/Filter Number:

SCHOTT BG36

Coating:
Uncoated

Color:
Clear

Index of Refraction n_d :
1.69

Surface Quality:
60-40

Transformation Temperature (°C):
657

Thickness (mm):
1.00 ±0.1

Type:
Bandpass Filter

Wavelength:
UV-IR

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
[View](#)