

SCHOTT BG42, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-377** ☐ In Stock

[Additional Bandwidths](#)

1

C\$57.40

ADD TO CART

Qty 1-10
C\$57.40
Qty 11+
C\$51.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
480.00

Density (g/cm³): 2.69
Glass/Filter Number: SCHOTT BG42
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 475
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--