

SCHOTT BG50, 165 x 110mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock **#16-902** CLEARANCE ☐ **In Stock**

-

1

+

C\$456.33

ADD TO CART

Qty 1+

C\$456.33

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
165.0 x 110.0 +3.0/-0.0

Density (g/cm³):
2.61

Glass/Filter Number:
[SCHOTT BG50](#)

Length (mm):
165.00

Coating:

Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Transformation Temperature (°C): 452
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 110.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--