

SCHOTT BG55, 50mm Sq., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-429** ☐ In Stock

-

1

+

C\$238.00

ADD TO CART

Qty 1-10
C\$238.00
Qty 11+
C\$212.80
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 514.00
Density (g/cm³):

2.64
Glass/Filter Number: SCHOTT BG55
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 453
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-Vis
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View