

SCHOTT BG60, 50mm Sq., 1mm Thick, Harsh Environment Colored Glass NIR Cut-Off Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-431** ☐ In Stock

- 1 +

C\$252.00

ADD TO CART

Qty 1-10
C\$252.00
Qty 11+
C\$222.60
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Center Wavelength CWL (nm):
500.00

Density (g/cm³):
2.83

Glass/Filter Number: SCHOTT BG60
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 411
Thickness (mm): 1.00 ±0.1
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View