


SCHOTT BG7, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-378** ☐ In Stock

[Additional Bandwidths](#)

1

C\$57.40

ADD TO CART

Qty 1-10
C\$57.40
Qty 11+
C\$51.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
488.00

Density (g/cm³): 2.61
Glass/Filter Number: SCHOTT BG7
Coating: Uncoated
Color: Deep Blue
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 468
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--