

SCHOTT N-WG305, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-405** ☐ In Stock

-

1

+

C\$44.80

ADD TO CART

Qty 1-10
C\$44.80
Qty 11+
C\$39.20
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 12.50
Cut-On Wavelength (nm): 305.00 ±6
Density (g/cm³):

2.51
Glass/Filter Number: SCHOTT N-WG305
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 420
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 99
Stopband Limit λ_s(nm): 260
Surface Quality: 60-40
Transformation Temperature (°C): 562
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--