

SCHOTT N-WG320, 50mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-471** ☐ In Stock

-

1

+

C\$108.50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| C\$108.50                     |
| Qty 11+                       |
| C\$106.40                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                                      |
|--------------------------------------|
| Get Product Downloads                |
| Dimensions (mm):<br>50.0 x 50.0      |
| Cut-On Wavelength (nm):<br>320.00 ±6 |
| Density (g/cm³):                     |

|                                                                |
|----------------------------------------------------------------|
| 2.51                                                           |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT N-WG320</a>  |
| <b>Length (mm):</b><br>50.00                                   |
| <b>Coating:</b><br>Uncoated                                    |
| <b>Color:</b><br>Clear                                         |
| <b>Passband Limit 1 <math>\lambda_{p1}</math> (nm):</b><br>470 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52           |
| <b>Spectral Transmittance <math>t_p</math> (%):</b><br>92      |
| <b>Stopband Limit <math>\lambda_s</math>(nm):</b><br>280       |
| <b>Surface Quality:</b><br>60-40                               |
| <b>Transformation Temperature (°C):</b><br>563                 |
| <b>Thickness (mm):</b><br>3.00 ±0.2                            |
| <b>Type:</b><br>Longpass Filter                                |
| <b>Wavelength:</b><br>UV                                       |
| <b>Width (mm):</b><br>50.00                                    |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                     |
| <b>Reflection Factor <math>P_d</math>:</b><br>0.92             |
| <b>Bevel:</b><br>Protective as needed                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |