

SCHOTT NG5 405nm 50mm Sq., 0.5 OD ND Filter



Stock **#21-367** ☐ In Stock

-

1

+

C\$231.00

ADD TO CART

Qty 1-9
C\$231.00
Qty 10+
C\$207.20
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
50.0 x 50.0 ±0.2

Optical Density OD (Average):
0.5 ±0.015 at Calibrated Wavelength

Clear Aperture CA (mm):
48.5 x 48.5

Design Wavelength DWL (nm):
405

Glass/Filter Number: Schott NG5
Coating: Uncoated
Surface Quality: 60-40
Transformation Temperature (°C): 474
Thickness (mm): 1.78 (nominal)
Transmission (%): 31.62 ±2.18 at Calibrated Wavelength
Type: Neutral Density Filter
Parallelism (arcmin): ≤3
Edges: Fine Grind
Bevel: 0.5 x45°
Shape of Back Surface: Plano

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View