

SCHOTT RG630, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-515** ☐ In Stock

- 1 +

C\$108.50

ADD TO CART

Qty 1-10
C\$108.50
Qty 11+
C\$106.40
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Cut-On Wavelength (nm): 630.00 ±6
Density (g/cm³):

2.65
Glass/Filter Number: SCHOTT RG630
Length (mm): 50.00
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 710
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 94
Stopband Limit λ_s (nm): 540
Surface Quality: 60-40
Transformation Temperature (°C): 527
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View