

SCHOTT RG9, 50mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-458** ☐ In Stock



1



C\$123.20

ADD TO CART

Qty 1-10

C\$123.20

Qty 11+

C\$109.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
50.00

Cut-On Wavelength (nm):
726.00

Density (g/cm³):

2.58
Glass/Filter Number: SCHOTT RG9
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 519
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--