

SCHOTT UG11, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT UG Glass (glass color will vary by product specification)

Stock **#16-944** [CONTACT US](#)

-

1

+

C\$1,240.40

ADD TO CART

Qty 1-10
C\$1,240.40
Qty 11+
C\$1,115.80
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.92
Glass/Filter Number: SCHOTT UG11

Length (mm): 165.00
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.56
Transformation Temperature (°C): 545
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--