



SCHOTT UG5, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-387** ☐ In Stock

[Additional Bandwidths](#)

1

C\$65.80

ADD TO CART

Qty 1-10
C\$65.80
Qty 11+
C\$57.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
318.00

Density (g/cm³): 2.85
Glass/Filter Number: SCHOTT UG5
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 462
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: UV
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--