

SCHOTT VG9, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT VG Glass (glass color will vary by product specification)

Stock **#16-945** ☐ In Stock

-

1

+

C\$707.00

ADD TO CART

Qty 1-10
C\$707.00
Qty 11+
C\$634.20
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.87
Glass/Filter Number: SCHOTT VG9

Length (mm): 165.00
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Transformation Temperature (°C): 462
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--