

SF10 25.4 x 25.4mm Ultrafast Prism



Stock **#89-844** ☐ In Stock

-

1

+

C\$281.40

ADD TO CART

Qty 1-5
C\$281.40
Qty 6+
C\$249.20
Volume Pricing
Request Quote

Get Product Downloads



Coating:

Uncoated

Substrate: ☐
[SF10](#)

Surface Quality:

40-20

Type:

Equilateral Prism
Dimensional Tolerance (mm): +0.0/-0.2
Angle Tolerance (arcmin): ±3
Bevel: <0.25mm x 45°
Clear Aperture (%): >80
Apex Angle (°): 60.60
Group Velocity Dispersion (fs²/cm): 1600.00
Surface Flatness (P-V): λ/10
Base Width (mm): 25.40
Base Length (mm): 25.4
Group Velocity Dispersion (fs²/mm): 155 @ 800nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
